

Component Labels for PanView iQ™ Patch Panels



Suggested Label Solutions for TIA/EIA-606-A Compliance

Patch Panel Part Number	Laser/Ink Jet Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
All Patch Panels on Page I.7	UILJ6	UILS8BW	UILS8BW

For complete Ultimate ID® Labeling Solutions and product information, reference charts on pages O.11 and O.19.

PanView iQ™ Patch Panels Fiber Trays

- Provides real-time physical layer management to the fiber channels in the network
- Enhances usability and maintainability through an enclosure and drawer design that allows for easy access to the fiber connectivity
- An easily-accessible integrated mechanism for mounting a PM or EM module simplifies installation and maintenance
- Provides the capability to map and monitor the fiber channels to efficiently manage resources and substantially reduce network operations cost
- Provides the capability to automate network documentation and maintenance procedures for the physical layer, which in turn supports improved reliability, security, and increased overall network management efficiency
- Installable in a 19" standard TIA/EIA rack or cabinet utilizing 1RU of space



PVQ-FMT

Part Number	Part Description	No. of Rack Spaces [^]	Std. Pkg. Qty.	Std. Ctn. Qty.
PVQ-FMT	24-port PanView iQ™ Fiber Tray with no fiber adapters.	1	1	1
PVQ-FMTMTP-ZX	24-port PanView iQ™ Fiber Tray including 24 (CMDSAQLCZBL) LC SR./SR. 10 Gig™ SFF duplex multimode aqua adapters with zirconia ceramic split sleeves.	1	1	1
PVQ-FMTMTP-9	24-port PanView iQ™ Fiber Tray including 24 (CMDSLCZBU) LC SR./SR. SFF duplex singlemode blue adapters with zirconia ceramic split sleeves.	1	1	1

[^]One rack space = 1.75" (44.45mm).