


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	PANEL THICKNESS	RECOM'D MTG HOLE DIA.	COLOR	WEIGHT
NR2WH-L	.170-.190(4.3- 4.8)	.320(8.1)	NATURAL (WHITE)	.07 LB/50 PCS (32g/50 PCS)
NR4BL-L	.220-.240(5.6-6.1)	.320(8.1)	BLACK	.07 LB/50 PCS (33g/50 PCS)
NR2WH-12	.170-.190(4.3- 4.8)	.320(8.1)	NATURAL (WHITE)	.02 LB/12 PCS (11g/12 PCS)
NR4BL-12	.220-.240(5.6-6.1)	.320(8.1)	BLACK	.02 LB/12 PCS (11g/12 PCS)

NOTES:

- NR2WH IS TO BE USED WITH PANDUIT 2X2 FIBEROPTIC DUCT AND FITTINGS. NR4BL IS TO BE USED WITH PANDUIT 4X4 FIBEROPTIC DUCT AND FITTINGS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



CAD FILENAME/LAYERS D36086BD_DC_NR2WH_NR4BL_02

PANDUIT

SNAP RIVET KIT
(NR2WH-L, NR4BL-L, NR2WH-12, NR4BL-12)
CUSTOMER DRAWING ^A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (XXX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY MAT'L

SCALE NONE

DATE 7/25/97

MAT'L NYLON

DWG NO. 36086-04

CHECKED BY HIW

SIZE A

REV	DATE	BY	CHK	ECN	CHK	CUST	SUP
R	7/25/97	DW	HIW	36086-04	HIW	HIW	

DESCRIPTION RELEASED TO PRODUCTION.



+

+