




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CPPKLA6ATG24WBL	.83 LB/EACH PC (376.5 g/EACH PC)



- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 - PART INCLUDES:
 - 1- INSTRUCTION SHEET
 - 1- ANGLED STAMPING
 - 6- FURNITURE FACEPLATES (CFFPL4)
 - 24- MINI-COM TX6A 10GIG UTP JACK MODULES
 - 1- TERMINATION TOOL
 - 1- #12-24 SCREW KIT (INCLUDES 4 SCREWS)
 - 1- M6 SCREW KIT (INCLUDES 4 SCREWS)
 - 6- LABEL
 - 6- LABEL COVER
 - DIMENSIONS IN [] ARE IN METRIC.



PART NUMBER	PRODUCT SPEC/PKG SPEC
CPPKLA6ATG24WBL	N/A
I.I. NUMBER	WORK INSTRUCTION
N/A	N/A

TITLE
MINI-COM 24 PORT ANGLED TX6A 10GIG UTP MODULAR PATCH PANEL KIT
CUSTOMER DRAWING
ITEM REVISION NAME
M00741NV/00

DATASET FILE NAME	PANDUIT
M00741NV_DC200/00A	

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL:
.x ± .1 [2.54] .xxx ± .005 [.127]	STAMPING: C.R.S.
.xx ± .01 [.25] ANGLES ± 5 °	FACEPLATES: ABS
DRAWING NUMBER:	
00741-200	

THIRD ANGLE PROJECTION	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
	BJN	6-24-13	JSP	NONE		A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	6-24-13	BJN	JSP	JSP	RELEASED TO PRODUCTION	00741-200

D10100DA/14

2

1

2

1