



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WEIGHT
DPA246X88TGY	1.26 lb (1070.48 g)



- NOTES:
- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
 - MATERIAL:
 PANEL HOUSING: STEEL
 RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0
 PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
 BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
 RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
 - 24 PORT ANGLED PATCH PANEL 8 POSITION 8 WIRE.
 - THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
 - FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) M6x1x15MM METRIC SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
 - DIMENSIONS IN BRACKETS ARE IN METRIC.
 - USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
 - RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.



MOUNTS TO 19" UNIVERSAL RACKS

CID**-C & CIP**-C, PHONE OR DATA ICON LOCATES HERE. IDENTIFIES INDIVIDUAL PORT. OPTIONAL, NOT SUPPLIED.

PART NUMBER		DPA246X88TGY	
TITLE			
DP6A 10GIG 24 PORT ANGLED PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479IY/00	
DATASET FILE NAME		M02479IY_DC235/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xx ± .03 (.8)		SEE NOTE 2	
.xxx ± .010 (.3)		DRAWING NUMBER:	
ANGLES ±		02479-235	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
LZ	3-04-06	CEF	.25-1
REV	DATE	BY	APR
1	5-30-14	MDJR	REFR
R	3-04-06	LZ	CEF

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5-30-14	MDJR	REFR	MMR	A. UPDATED TITLE BLOCK.	02479-235
R	3-04-06	LZ	CEF	CEF	RELEASED TO PRODUCTION	02479-235

D101000DA/14