





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
JA0SSPTP**	.23 LB/10 PCS (106.2 g/10 PCS)

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
  2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
  3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
  4. PARTS INCLUDED IN KIT:  
(1) - ADAPTER WITH OPAQUE DOOR AND LAN/CAT6 PRINT  
(1) - MINI-COM TX6 PLUS JACK MODULE



PART NUMBER		JA0SSPTP**	
TITLE			
MINI-COM 1 POSITION JIS SPRING SHUTTERED ADAPTER KIT			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02079AN/00	
DATASET FILE NAME		M02079AN_DC08/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .03 (.8)		ADAPTER - ABS	
.xxx ± .010 (.3)		DOOR - PC	
ANGLES ±		SPRING - SPRING STEEL	
DRAWING NUMBER:		02079-08	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
JSP	8-1-05	JCO	NONE
REV	DATE	BY	CHK
2	6-25-14	MDJR	REFR
APR	DESCRIPTION		ECN
MMR	A. UPDATED TITLE BLOCK. REMOVED ALL PREVIOUS REVISIONS FOR CLARITY.		02079-08

D10100DA/14