



PANDUIT P/N	WEIGHT
V1B1B1D0A30AHA0	8.2kg (18.1lb)

NOTES:


- IDENTIFICATION: VERTICAL, MIXED (18) LOCKING C13 AND (6) LOCKING C19, BASIC 120V / 20A / SINGLE-PHASE PDU
- PART NO. V1B1B1D0A30AHA0 COLOR BLACK
- ACCESSORY COMPONENTS: (1) QUICK-START GUIDE
- PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
- RoHS COMPLIANT.
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- MAXIMUM AVAILABLE INPUT POWER = 1.9 kW
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
- PRINTED WITH PHASE & CIRCUIT IDENTIFICATION.



BOTTOM VIEW



TOP VIEW



SIDE VIEW

PLUG
20 AMP, 125V
TWIST-LOCK
NEMA L5-20P

EIGHTEEN (18)
LOCKING RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

SIX (6)
LOCKING RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

00A	09-19-14	SAT	MRWA		RELEASED TO PRODUCTION	12V092G1-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.

THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

TITLE: V1B1B1D0A30AHA0

CUSTOMER DRAWING

ITEM REVISION NAME: 12V092G1/00

DATASET FILE NAME: 12V092G1_DC/00A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 INCHES: X.X +/- 0.03, X.XX +/- 0.018, X.XXX +/- 0.007
 METRIC - MILLIMETER: X +/- 0.8, X.X +/- 0.46, X.XX +/- 0.18
 ANGLE: +/- 1°

MATERIAL: N/A

DRAWING NUMBER: 12V092G1-DC

DRAWN BY: SAT DATE: 09-16-14 CHK: MRWA SCALE: NONE

THIRD ANGLE PROJECTION

SHT 1 OF 1 SIZE B