




PANDUIT P/N	WEIGHT
P1N1B1COA10AKA0	3.70kg (8.15lb)



REAR VIEW




FRONT VIEW




SIDE VIEW

- NOTES:
- IDENTIFICATION: HORIZONTAL, (10) NEMA 5-20R, NETWORKED, 120V / 20A / SINGLE PHASE PDU
 PART NO. PIN1B1COA10AKA0 COLOR BLACK
 - ACCESSORY COMPONENTS:
 (1) QUICK-START GUIDE
 (4) #12-24 SCREWS
 (4) M6 x 20mm SCREWS
 - PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
 - CIRCUIT LEVEL POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED VIA ETHERNET CONNECTION OR ON-UNIT DISPLAY.
 - RoHS COMPLIANT.
 - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
 - MAXIMUM AVAILABLE INPUT POWER = 1.9 kW
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



PLUG
20 AMP, 125V
STRAIGHT BLADE
NEMA 5-20P



TEN (10)
RECEPTACLES
20 AMP, 125V
STRAIGHT BLADE
NEMA 5-20R

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	04/30/14	PJST	MRWA	EDM	RELEASED TO PRODUCTION	12V092EU-DC

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.		SIGN
THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		DATE
		PRINT
TITLE P1N1B1COA10AKA0		
CUSTOMER DRAWING		
ITEM REVISION NAME 12V092EU/00.PRT		PANDUIT
DATASET FILE NAME 12V092EU_DC/00A.PRT		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR: N/A
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007	METRIC - MILLIMETER X.X +/- 0.8 X.X +/- 0.46 X.XX +/- 0.18	ANGLE +/- 1°
THIRD ANGLE PROJECTION		DRAWING NUMBER: 12V092EU-DC
DRAWN BY PJST	DATE 04/30/14	CHK MRWA
SCALE NONE		SIZE B
SHT 1 OF 1		