


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SRB19BLY	1.7 LB/10 PCS (771.1 g/10 PCS)

NOTES:


1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- STRAIN RELIEF BAR
 - 1- SCREW KIT (INCLUDES 4 SCREWS)



MODEL FILENAME	M00742ET_STRN_BAR_05.PRT	SIZE	A
DRAWING FILENAME	M02479DW_DC103_00A.PRT		

NETWORK SYSTEMS
MAY 25 2006
ENGINEERING DEPT

STRAIN RELIEF BAR
CUSTOMER DRAWING



ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .010(.3)
(.XX) ± .001(.01) ANGLES ±

I.I. NUMBER	N/A
PRODUCT SPEC	N/A
WORK INSTRUCTION	N/A
SCALE	NONE
PART NO.	SRB19BLY
DRAWING NO.	02479-103

DRAWN BY	JsP
DATE	4-18-06
CHK'D	MJD

REVIEW DRAWING NUMBERS
MATERIAL: STEEL BAR STOCK

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	4-18-06	JsP	MJD	RELEASED TO PRODUCTION	02479-103		MJD	MJD	