



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. KIT INCLUDES:
 - A. PATCH PANEL COMPONENTS:
 - 1 - METAL STAMPING
 - 6 - (4) POSITION ABS PLASTIC FACEPLATE (ASSEMBLED TO METAL STAMPING)
 - 1 - SCREW KIT (INCLUDES (4) #12-24 SCREWS)
 - 1 - SCREW KIT (INCLUDES (4) M6 SCREWS)
 - B. CABLE ASSEMBLY:
 - 48 - CAT 6 UTP 28 AWG CM/LSZH CABLE ASSEMBLY, 8 INCHES LG, COLOR: BLUE (PACKAGED IN (2) BAGS OF (24))
 - C. STRAIN RELIEF BAR:
 - 1 - STRAIN RELIEF BAR, EXTENDED 5" W/MOUNTING HARDWARE
2. CABLE ASSEMBLIES & STRAIN RELIEF BAR ARE NOT ASSEMBLED TO PATCH PANEL.
3. PATCH PANEL ACCEPTS SNAP-IN MINI-COM MODULES.
4. DIMENSIONS IN PARENTHESES ARE METRIC.
5. TOTAL WEIGHT PER (1) ASSEMBLY IS: 3.31 LBS (1497 grams).

PART NUMBER CPP48KFVPCBU		PRODUCT SPEC/PKG SPEC N/A	
I.I. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE MINI-COM 48 PORT FLUSH MOUNT PANEL KIT W/VERTICAL NUMBERING SEQUENCE, INCLUDES 8IN BLUE PATCH CORDS & STRAIN RELIEF BAR CUSTOMER DRAWING			
ITEM REVISION NAME M01668AA/03		PANDUIT	
DATASET FILE NAME M01668BI_DC18/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: PANEL: C.R.S. FACEPLATE: ABS	
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		DRAWING NUMBER: 01668-18	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY BJN	DATE 3-21-13	CHK DCS	SCALE .25:1
DESCRIPTION		ECN 01668-18	SIZE A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	3-21-13	BJN	DCS	DCS	RELEASED TO PRODUCTION	01668-18

D10100DA/14