



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO. *	WEIGHT
MIWBA	8.6 LB/100 PCS (3909 g/100 PCS)



NOTES:

- * 1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- 2. SEE CURRENT CATALOG FOR VARIOUS MOUNTING APPLICATIONS.
- △ 3. THE FOLLOWING SCREWS ARE PROVIDED:
 - a. FOUR (4) #6-32 X 1" SLOTTED PAN HEAD MACHINE SCREWS. (* PAINTED)
 - b. TWO (2) #8-32 X 1" SLOTTED PAN HEAD MACHINE SCREWS. (* PAINTED)
 - c. TWO (2) #6-20 X 1/2" SLOTTED PAN HEAD TYPE B SHEET METAL SCREWS. (SELF-TAPPING SCREW) (* PAINTED)
 - d. TWO (2) #6-20 X 1/4" SLOTTED PAN HEAD TYPE B SHEET METAL SCREWS. (SELF-TAPPING SCREW) (NOT PAINTED)
 (* SCREWS ARE PAINTED TO MATCH ADAPTER COLOR.)
- 4. DIMENSIONS IN PARENTHESES ARE IN METRIC.

DPC 34304 MIWBA C (D)

CAD FILENAME/LAYERS

PANDUIT CORP. TINLEY PARK, ILLINOIS

IN-WALL BOX ADAPTER (MIWBA) CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ± .010 (.3)
 (.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
1	2/22/93	DW		A. ADDED SCREW REFERENCE NOTE 3.	34304-1			
R	6-8-92	DW	CEF	RELEASED TO PRODUCTION	34304-1			

DRAWN BY DW	MAT'L: ABS (UL 94V-0)
DATE 5-19-92	
CHECKED BY JF	

SCALE NONE
DRAWING NO. 34304-1
DWG SIZE A