



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	TYPE	FOR USE WITH
FLCDS3.0BU	SINGLEMODE	9/125um FIBER
FLCDM3.0BL	MULTIMODE	50/125um FIBER
FLCDM3.0E1	MULTIMODE	62.5/125um FIBER

NOTES:

1. SEE CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. ACCEPTS 3.0mm SINGLEMODE, 50/125um MULTIMODE OR 62.5/125um MULTIMODE GLASS OPTICAL FIBER.
3. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3.
4. MATERIAL:
 BODY/HARDWARE: PLASTIC
 BOOT: THERMOPLASTIC RUBBER
 FERRULE: ZIRCONIA CERAMIC
5. DIMENSIONS IN BRACKETS ARE METRIC [mm].
6. WEIGHT PER 10 PIECES, .069 lb [31.3g].



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	04-15-10	MC		RELEASED TO PRODUCTION	01371-53				

FIBER OPTIC SINGLEMODE/MULTIMODE
 DUPLEX LC CONNECTOR WITH 3.0mm BOOTS
 CUSTOMER DRAWING

PANDUIT™
 CORP.
 TINLEY PARK, ILL 60477

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
 DIMENSIONAL TOLERANCES ARE:
 (.X) ±.03 | (.XXX) ±.010 | (.3) ±.005 | (.XX) ±.03 | (.8) ANGLES

THIRD ANGLE PROJECTION

DRAWN BY: MC
 DATE: 09-17-07
 CHK'D: JDK

REVIEW DRAWING NUMBERS: AS NOTED

DRAWING FILENAME: MO1371ZT_DC/02A
 SCALE: NONE
 PART NO.: FLCDS3.0BU
 FLCDM3.0BL/FLCDM3.0E1
 DRAWING NO.: 01371-53
 SIZE: A