





PANDUIT P/N	WEIGHT
H1B1B1L2N10BCA0	4.6kg (10.24lbs)


NOTES:  
 1. IDENTIFICATION: 1 RU HORIZONTAL, (8) C13 & (2) C19, BASIC, 208V / 30A / SINGLE-PHASE PDU

PART NO. H1B1B1L2N10BCA0 COLOR BLACK


2. ACCESSORY COMPONENTS:  
 (1) QUICK-START GUIDE  
 (4) M6 X 20mm SCREWS  
 (4) 12-24 X 1/2" SCREWS
3. PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES].
4. RoHS COMPLIANT.
5. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
6. MAXIMUM AVAILABLE INPUT POWER = 4.9 kW
7. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.
8. PRINTED WITH PHASE & CIRCUIT IDENTIFICATION.



PLUG  
 30 AMP, 250V  
 TWIST LOCK  
 NEMA L6-30P



EIGHT (8)  
 RECEPTACLES  
 15 AMP, 250V  
 STRAIGHT BLADE  
 IEC 60320/C13



TWO (2)  
 RECEPTACLES  
 20 AMP, 250V  
 STRAIGHT BLADE  
 IEC 60320/C19

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00B	8/20/15	MRWA	RGO	EDM	A. DRAWING WAS INCORRECTLY LABELED AS A CONTROL DRAWING	12V092GE-DC
00A	09/19/14	SAT	MRWA	EDM	RELEASED TO PRODUCTION	12V092GE-DC

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.  
 THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

TITLE: H1B1B1L2N10BCA0  
 CUSTOMER DRAWING

ITEM REVISION NAME: 12V092GE/00  
 DATASET FILE NAME: 12V092GE\_DC/00B

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
 INCHES: X.X +/-, X.XX +/-, X.XXX +/-  
 METRIC - MILLIMETER: X +/-, X.X +/-, X.XX +/-  
 ANGLE: +/-

MATERIAL/COLOR: N/A

DRAWING NUMBER: 12V092GE-DC

DRAWN BY: SAT DATE: 09/16/14 CHK: MRWA SCALE: NONE

SHT 1 OF 1 SIZE: B