


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:



1. SYSTEM INCLUDES:

- (1) PULS 240W 24 VOLT DC POWER SUPPLY (CP10.241-S1)
  - (1) ROCKWELL 91.2W 24 VOLT DC POWER SUPPLY (1606-XLSDNET4)
  - (2) 100 WATT 24 VOLT DC PANDUIT UPS (UPS00100DC)
  - (2) PANDUIT LSM (UPS003LSM)
  - (2) STAHL 10 AMP LOCKOUT CONTACT BLOCKS (8082/1-1-01)
  - (2) WEIDMULLER RED AND WHITE TERMINAL BLOCKS FOR INCOMING POWER (100-240 VAC 50-60HZ)
  - (1) PANDUIT 6-PORT GROUND BAR
2. POWER CIRCUIT DESIGNED FOR TWO 24 VOLT DC INDUSTRIAL ETHERNET SWITCHES NOT TO EXCEED 42 WATTS PER SWITCH
  3. ALL ACTIVE COMPONENTS RATED FOR USE CLASS 1, DIVISION 2 ENVIRONMENTS
  4. ALL ZONE SYSTEMS COMPLY WITH UL 508A STANDARDS
  5. ALL ZONE SYSTEMS REQUIRE A 100-240 VOLT AC SINGLE-PHASE FEED
  6. INTERNAL WIRING NOT SHOWN, SEE DRAWING (15V510RK) FOR COMPLETE SCHEMATIC

|   |          |  |       |            |
|---|----------|--|-------|------------|
| TITLE   |          | NETWORK ZONE SYSTEM, 100-240VAC INPUT, REDUNDANT 24VDC POWER SUPPLIES, TWO 24VDC PANDUIT UPS |       |            |
| CUSTOMER DRAWING  |          |  |       |            |
| ITEM REVISION NAME  |          | 15V510JJ/02  |       |            |
| DATASET FILE NAME   |          | 15V510JJ_DC/02A  |       |            |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] |          | MATERIAL:  |       |            |
| .x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ]                        |          | N/A  |       |            |
| .xx ± .01 [ .25 ]      ANGLES ± 5 °                               |          | DRAWING NUMBER:  |       |            |
| THIRD ANGLE PROJECTION  |          | 15V510JJ   |       |            |
| DRAWN BY  | DATE     | CHK  | SCALE | SHT 1 OF 1 |
| JBO   | 10/26/16 | NWW  | 1:4   | A          |

| 02A | 2/1/18 | RHG | NWW | TIMH | RELEASED TO CUSTOMER | ECN-INI-0001/01 |
|-----|--------|-----|-----|------|----------------------|-----------------|
| REV | DATE   | BY  | CHK | APR  | DESCRIPTION          | ECN             |

10/100DA/14